


# E10867



## Connecting cable with socket

ADOGH030MSS0002E03



### Electrical data

Operating voltage [M] < 250 AC / < 300 DC

### Operating conditions

Ambient temperature [°C] -25...90

Protection IP 67

### Mechanical data

Weight [g] 87.8

Dimensions [mm] 15 x 15 x 43

Materials TPU

Material nut brass, nickel-plated

### Remarks


Pack quantity 1 pcs.

### Electrical connection

Cable: 2 m, PVC, orange, Ø 5 mm; 3 x 0.34 mm<sup>2</sup> (19 x Ø 0.16 mm) / AWG 22

### Electrical connection - socket

Connector: 1 x M12, straight; Moulded body: TPU; Locking: brass, nickel-plated; Tightening torque: 0.5 Nm




# E10867



## Connecting cable with socket

ADOGH030MSS0002E03

### Connection



Core colours :

BK = black

BU = blue

GN/YE = green/yellow