


E21138



Ethernet connection cable

VSTGN040ZDS0002L04STGN04ZDS



| Application | |
|---|---|
| Special feature | Gold-plated contacts; Screened cable |
| Design | Ethernet cable, D-coded |
| Electrical data | |
| Operating voltage [V] | < 50 AC / < 60 DC |
| Protection class | III |
| Max. current load total [A] | 4 |
| Operating conditions | |
| Ambient temperature [°C] | -20...90 |
| Protection | IP 67 |
| Mechanical data | |
| Weight [g] | 163.5 |
| Dimensions [mm] | 15 x 15 x 47.3 |
| Materials | TPU |
| Material nut | diecast zinc, nickel-plated / diecast zinc, nickel-plated |
| Remarks | |
| Pack quantity | 1 pcs. |
| Electrical connection - plug | |
| Connector: 1 x M12, straight; Moulded body: TPU; Locking: diecast zinc, nickel-plated; Contacts: gold-plated; Shielded connection cable: screen connected | |

E21138



Ethernet connection cable


VSTGN040ZDS0002L04STGN04ZDS



Electrical connection

Cable: 2 m, PVC, green, shielded; 4 x 0.34 mm²

Connection



Electrical connection - plug

Connector: 1 x M12, straight; Moulded body: TPU; Locking: diecast zinc, nickel-plated; Contacts: gold-plated; Shielded connection cable: screen connected

