


MIRO,TR,24VDC,24VDC 6A SK OPTO-COUPLER MODULE


IN: 53 VDC - OUT: 48 VDC / 6 A

Transistor 6 A
24 V DC
Screw terminals

[Link to Product](#)

Illustration





Product may differ from Image

Approvals



Input

Voltage range ON	10...53 V DC
Voltage range OFF	0...5 V DC
Control current	approx. 10 mA
LED display	LED (yellow)

General data

Test isolation voltage	2.75 kV
Mounting method	DIN-rail mountable (EN 60715)
Housing	Black plastic, flame retardant
Temperature range	-20...+60 °C
Dimensions H × W × D	78×6.2×65 mm

Output

Switching voltage	5...48 V DC
Switching current per output	1 mA...6 A (without derating)
Saturation voltage (across output)	max. 0.1 V DC
Leakage current (output is open)	max. 25 µA
Switching time ON/OFF	2/5 ms
Switching frequency	max. 1/0.1 Hz (resist./ind.)

Commercial data

country of origin	CZ
customs tariff number	85414090
minimum order quantity	1