

## IT18FL9C2

**Article Number: 111-81919**

**Identification Tie, 4.3" Long, 18lb Tensile Strength, PA66, Natural, 100/pkg**



Download drawing



Download spec sheet

### Base Data

**Local Order Number** IT18FL9C2

**Type** IT18FL

**Color** Natural (NA)

- Features and Benefits**
- Identification plate feature allows bundles to be easily marked and identified.
  - Wire and cable harnesses can be secured and identified using just one product, which saves time.
  - Plates can be marked manually with a permanent marker or with a pre-printed adhesive label.

**Product Description** HellermannTyton Identification cable ties feature an identification plate allowing wire and cable bundles to be easily marked and identified. These ties enable wire and cables to be secured and identified using just one product, saving installation time. The plates can be marked using a permanent marker or with a HellermannTyton adhesive label.

**Mounting method Identification ETIM** Others

**Short Description** Identification Tie, 4.3" Long, 18lb Tensile Strength, PA66, Natural, 100/pkg

### Product Dimensions

**Minimum Tensile Strength (Imperial)** 18.0 lbs

**Minimum Tensile Strength (Metric)** 80.0 N

**Length L (Imperial)** 4.3 "

**Length L (Metric)** 110.0 mm

**Fixation Method** None

**Identification Plate Position** stands of bundle

**Tie Closure** plastic pawl

**Variant** Inside Serrated

**Width W (Imperial)** 0.81 "

**Width W (Metric)** 20.5 mm

**Width W2 (Imperial)** 0.1 "

**Width W2 (Metric)** 2.5 mm

**Height H (Imperial)** 0.35 "

**Height H (Metric)** 9.0 mm

**Bundle Diameter Min. (Imperial)** 0.06 "

**Bundle Diameter Min. (Metric)** 1.5 mm

**Bundle Diameter Max. (Imperial)** 0.75 "

**Bundle Diameter Max. (Metric)** 19.0 mm

**Outside Diameter Min. (Imperial)** 0.059 "

**Outside Diameter Min. (Metric)** 1.50 mm

**Outside Diameter Max. (Imperial)** 0.75 "

**Outside Diameter Max. (Metric)** 19.00 mm

---

## Logistics and Packaging

---

**Quantity Per** bag  
**Package Quantity (Metric)** 100 Pieces  
**Carton Quantity** 10000 Pieces  
**Weight (Metric)** 0.3 kg

---

## Material and Specifications

---

**Material** Polyamide 6.6 (PA66)  
**Material Shortcut** PA66  
**Flammability** UL94 V2  
**Halogenfree** Yes  
**Operating Temperature** -40°F to +185°F (-40°C to +85°C)  
**ROHS Compliant** Yes  
**Certification/Specification** UL-Recognized  
**UL Listed (US and Canada)** No  
**UL Recognized (US and Canada)** Yes