

Hot air tool

HL Stick

EAN 4007841 004019

Article number 004019



CE



VDE

Function description

Hands free. Compact hot air gun HL Stick for heating with pinpoint precision, ideal for craft and model-making. Practical, easy to grip and lightweight, hand-held and self-resting tool in one, sensational standing stability, with integrated LED work light, includes 4 attachment nozzles. red dot design award: The HL Stick was given the red dot product design award 2013 for its design.

Technical specifications

Temperature	400 – 500 °C	Replaceable heating element	No
Airflow rate	100 l/min	Restart protection	No
Temperature setting	Continuous	Temperature scanner	No
Settings made via	multiple-stage switch	Fine dust filter	No
Airflow control	Settings	Thermal cut-out	Yes
Programming function	No	Thermostat	No
Residual heat indicator	No	ESD	No
Cool function	No	Nozzle receiver, type	19
Motor, type	Brush motor	Cord length	2.2 m
Heating element	Ceramic heating element	Dimensions (L x W x H)	235 x 78 x 76 mm
Mains power supply	220 – 230 V / 50 Hz	PU1, net weight	0,594 kg
Function, hanger	Yes	Manufacturer's Warranty	3 years
Function, life expectancy, motor	250 h	PU1, EAN	4007841004019
Function, life expectancy, heating element	250 h		

Hot air tool

HL Stick

EAN 4007841 004019
Article number 004019



Accessories

EAN 4007841 002886	Reduction nozzle 7 mm
EAN 4007841 077358	Reduction nozzle with reflector guard
EAN 4007841 077556	Reflector nozzle 10 mm
EAN 4007841 077655	Reflector nozzle 40 mm