

Pneum. contact metal OD 3 female+valve



Part number	09 14 000 6463
Specification	Pneum. contact metal OD 3 female +valve
HARTING eCatalogue	https://b2b.harting.com/09140006463

Image is for illustration purposes only. Please refer to product description.

Identification

Category	Contacts
Type of contact	Pneumatic contact
Description of the contact	With shut-off Straight
Version	
Gender	Female
Manufacturing process	Turned contacts
Technical characteristics	
Limiting temperature	-20 +85 °C Tube outer diameter
Operating pressure	≤10 bar
Tube outer diameter	3 mm
Material properties	
Material (contacts)	Brass
Material (seal)	HNBR (hydrated NBR)
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained

Page 1 / 2 | Creation date 2023-01-05 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application. HARTING Stiftung & Co. KG | Marienwerderstr. 3 | 32339 Espelkamp | Germany



Material properties

REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	b51e5b97-eeb5-438b-8538-f1771d43c17d
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
	Nickel
	Naphthalene

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Commercial data	
Packaging size	10
Net weight	13 g
Country of origin	Germany
European customs tariff number	39269097
GTIN	5713140189201
eCl@ss	27440204 Contact for industrial connectors