

Product information

87 05 300

KNIPEX Cobra®

High-Tech Water Pump Pliers

DIN ISO 8976

- Push the button for adjustment on the workpiece
- Fine adjustment for optimum adaptation to different sizes of workpieces and a comfortable handle width
- Self-locking on pipes and nuts: no slipping on the workpiece and low handforce required
- Gripping surfaces with special hardened teeth, teeth hardness approx. 61 HRC: high wear resistance and stable gripping
- Box-joint design for high stability due to double guide
- Reliable catching of the hinge bolt: no unintentional shifting
- Pinch guard prevents operators' fingers being pinched
- Chrome vanadium electric steel, forged, multi stage oil-hardened



General

Article No.	87 05 300
EAN	4003773014126
Pliers	chrome-plated
Head	polished
Handles	with multi-component grips
Weight	580 g
Dimensions	300 x 48 x 16 mm
Standard	DIN ISO 8976
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Adjustment positions	30
Kapazität für Rohre (Zoll)	Ø 2 3/4 Inch
Capacities for nuts	60 mm
Capacities for pipes (diameter)	Ø 70 mm

technical change and errors excepted



