

Product information

97 52 63 DG

Four-Mandrel Crimping Pliers for turned contacts




- Crimping capacity can be adjusted in increments of 0.01 mm
- With digital display of the preset crimping capacities and possibility of re-calibration via RESET function with electronic wear monitoring
- Adjustment in mm, inches or comparable selection positions according to MIL
- Pliers in a plastic case with foam insert and standard locator for precise positioning of the contacts
- For crimping turned contacts
- Four-mandrel crimping for top-quality crimping connections
- Mandrel gauge to check the basic setting
- Repetitive, high crimping quality due to ratchet mechanism (unlockable)
- Optimum transmission of force due to highly effective lever action for fatigue-reduced operation
- High operation comfort thanks to handy shape
- Special quality chrome vanadium electric steel, oil-hardened



General

Article No.	97 52 63 DG
EAN	4003773063209
Pliers	chrome-plated
Head	chrome-plated
Handles	with multi-component grips
Weight	388 g
Dimensions	195 x 82 x 19 mm
REACH compliant	contains SVHC
RoHS compliant	not applicable

Technical details



Application	turned contacts
Capacity in square millimetres	0.08 — 2.5 mm ²
AWG	28 — 14
Number of crimping positions	1
Max. contact diameter	5 mm

technical change and errors excepted



Standard locator