

Clamping heads, round version

ORION®

Application:

Versatile in application, machining centres, all common axial force clamping systems on lathes and vices, measuring machines or pallet clamping.

Execution:

- High-strength rubber/metal connection
- High retention forces
- Corrosion protection coating

Art. no.	22001 024
Brand	ORION
Manufacturer Part Number	22001024
Size	32
Design	Without stem
Profile shape	Round and smooth
Clamping diameter	26 mm
Length	44 mm
Min./max. clamping range diameter	3-32 mm
Gross Weight	0.340 kg
Product Group	2AO



EAN

4053625466405