

Collet chucks type ER40 in accordance with DIN 6499 A

HP = high precision, concentricity < 5 µm

ATORN[®]

Application

For use on precision collet chucks

Advantage

- Higher concentricity extends tool life

| | |
|---------------------------------|------------------|
| Art. no. | 23388 112 |
| Collet type | ER 40 |
| Clamping diameter | 14 mm |
| Min./max. clamping range | 3-26 mm |
| Outer diameter | 41 mm |
| Length | 46 mm |
| Clamping bypass | -0.5 mm |



EAN-Code

4050293630800