

push rod clamp with variable clamping height

with angular base



Application:

Quick-action clamp with infinitely adjustable balancing function for workpieces with different clamping widths.

Version:

- galvanised and passivated.
- ergonomic, oil-resistant handle with large hand rest and soft components.
- protection against the loss of the clamping screw on the end of the clamping arm. complete with zinc-plated clamping bolt
- Size 15 clamping bolt M6 x 29 mm
- Size 25 clamping bolt M8 x 38 mm

Advantage:

- variable clamping height, for clamping different workpieces
- used for small lot sizes
- infinitely adjustable clamping force
- ergonomic 2 component handle
- protection against loss on clamping arm



Art. no.	26217 115
Size	15
Distance	8.5 mm
Min./max. clamping width	42-59 mm
Min./max. length	20-26 mm
Drill hole	5.6 mm
Drill hole 2	5.6 mm
Length 2	20 mm
Height	66 mm
Overall height of lower handle	91 mm
Clamping stroke	9 mm
Overall height of upper handle	173 mm
Thread dimension	M6
Distance 2	7.1 mm
Length	167 mm
Base plate width	45 mm
Hole distance 3	25.4 mm
Base plate length	38 mm
Tension force	2 kN
Height 2	8 mm
Height 3	13 mm

EAN-Code

4020772003692