

Adjustable clamps

Short and infinitely adjustable with U-piece



Application:

For clamping workpieces.

Version:

- With U-piece
- Suitable for tough conditions, e.g. on presses
- Tempered
- Galvanised and blue passivated
- Infinitely adjustable

Delivery:

With U-piece, though without clamping screw



Art. no.	26225 020
For table grooves according to DIN 650	16 mm, 18 mm
Min./max. clamping height	0-55 mm
Min./max. clamping height 2	42-84 mm
Clamping shoe length	130 mm
Clamping shoe width	56 mm
Bore diameter	18 mm
Distance 2	74 mm
Distance	29 mm
Distance 1	38 mm
Distance 3	18 mm
Suitable screw DIN 787	M16 x 160 mm
Slot nut width of clamping screw	16 mm, 18 mm
Height	84 mm

EAN-Code

4020772073947