

Folding door cabinet, height 1950 mm

With shelf, load capacity 80 kg per shelf

Execution:

- Stable, welded steel sheet structure with base
- Galvanised shelves, height-adjustable in increments of 17 mm
- Practical, inset-type folding doors with internal pivot pins, doors reinforced by box-type profile on inside, approx. 125° door opening angle
- Locks by means of turning handle with triple-point security cylinder lock, incl. 2 keys

Advantage:

- With the folding-door mechanism, more space is provided; ideal for use in narrow passageways or in tight workplaces
- An even better view into the cabinet since large door surfaces no longer block the way

Delivery:

On request: Load capacity per shelf 100 kg with evenly distributed load, DOM locking system (suitable for HK tool cabinets, HK tool shelves, HK workbenches, HK hinged-door and sliding-door cabinets). Other colours available on request.



| | |
|---|--|
| Art. no. | 50045 421 |
| Brand | PAVOY |
| Manufacturer Part Number | 39393-120-400 |
| Door design | Full-sheet panel |
| Height | 1950 mm |
| Depth | 400 mm |
| Width | 1200 mm |
| Number of shelves | 4 PCS |
| Load-carrying capacity per shelf | 80 kg |
| Number of folder height | 5 PCS |
| Load-carrying capacity | 400 kg |
| With partition wall | No |
| Lock type | Twist-grip lock with three-point fastening |
| Material | Sheet steel |
| Cabinet colour | Light grey RAL 7035 |
| Colour of front | Light grey RAL 7035 |
| Surface | Powder-coated |
| Gross Weight | 7 1.000 kg |
| Product Group | 5CB |