




EGB PACKINGS FOR ELECTRONIC PARTS (LIASTAT*)



Art. No.	V 3-12-6-6-10-10	V 3-18-6-6-10-10	V 3-30-6-6-10-10	V 3-40-6-6-10-10
Inside dimensions	50 x 30 x 16	57 x 36 x 17	73 x 42 x 17	80 x 50 x 27
Art. No.	V 3-12/9-6-10	V 3-18/9-6-10	V 3-30/9-6-10	V 3-40/9-6-10
Foam fit for insertion	8 mm	8 mm	8 mm	8 mm
Colours	●	●	●	●



Art. No.	V 8-14 SCH + V-6-6-10-10	V 9-40 SCH + V-6-6-10-10	V 8-12 SCH + V-6-6-10-10
Outside dimensions	295 x 175 x 20	295 x 175 x 20	80 x 50 x 27
Inside dimensions	292 x 160 x 16	73 x 42 x 17	80 x 50 x 27
Colours	●	●	●
Note	various compartment inserts s. p. 29-30, conductive versions on request	54 compartments	various comp. inserts s. p. 28-29, conductive versions on request




Art. No.	V 8-8-6-6-10-10	V 8-9 SCH + V-6-6-10-10	V 8-15-6-6-10-10
Inside dimensions	183 x 108 x 30	196 x 136 x 49 (Outside dimensions 203 x 152 x 53)	220 x 130 x 35
Art. No.	V 8-8/9-6-10		
Foam fit for insertion	8 mm		
Colours	●	●	



Stackable boxes, slip lid
EGB foam inlays on request

Art. No.	V 3-16-6-6-10-10	55 x 55 x 25/16 inside
Art. No.	V 3-17-6-6-10-10	55 x 55 x 35/26 inside
Art. No.	V 3-59-6-6-10-10	115 x 55 x 35/26 inside
Art. No.	V 3-60-6-6-10-10	115 x 55 x 55/46 inside
Art. No.	V 3-61-6-6-10-10	115 x 115 x 55/46 inside



Stackable boxes, slip lid
EGB foam inlays on request

Art. No.	V 8-1-6-6-10-10	75 x 50 x 33 inside
Art. No.	V 8-2-6-6-10-10	75 x 50 x 45 inside
Art. No.	V 8-5-6-6-10-10	106 x 75 x 46 inside
Art. No.	V 8-7-6-6-10-10	56 x 106 x 46 inside



Liastat hinged boxes

Art. No.	V 20-29-6-10	130 x 80 x 14 inside
Art. No.	V 20-30-6-10	130 x 80 x 30 inside
Art. No.	V 20-31-6-10	130 x 80 x 50 inside
Art. No.	V 20-32-6-10	178 x 133 x 78 inside
Art. No.	V 20-33-6-10	221 x 121 x 55 inside

Dimensions in mm. EGB flexible foam or foam fit for insertion on request. *Liastat = material conductive.

Dimensions subject to errors and corrections!