

VOLTCRAFT - TOP PERFORMANCE IN EVERY WAY

For more than 40 years, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft's success.

LX-80 ANEMOMETER



Item no: 2620278

The product is a handheld anemometer with temperature measurement.

CONTENTS

Anemometer // 3x AAA 1.5 V batteries // Carry bag // Operating instructions

TECHNICAL DATA

General

Power supply	3x AAA 1.5 V batteries
Battery life	approx. 10 hrs (continuous use)
Auto shut-off	15 mins
Ingress protection	IP54
Operating altitude	≤2000 m
Operating conditions	0 °C to +50 °C
Storage conditions	-10 °C to +60 °C, <80 % RH (non-condensing)
Dimensions (W x H x D)	48 x 220 x 27 mm
Weight	135 g

Measurement specifications

Measurement	units	Range	Accuracy
Wind speed	m/s	0.3 to 30	3% ±0.5
	ft/min	59 to 5905.8	3% ±90.4
	knots	0.5 to 58.3	3% ±0.9
	km/h	1 to 108	3% ±1.8
	MPH	0.6 to 67.2	3% ±1.1



Measurement	units	Range	Accuracy
Temperature	°C	-10 to +50	±2 °C
	°F	+14 to +122	±4 °F
Air volume	ft ³ /min	0 to 99999	-
	m ³ /min	0 to 99999	-

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com).

All rights including translation reserved. Reproduction by any method (e.g. photocopying, microfilming or the capture in electronic data processing systems) requires prior written approval from the editor. Reprinting, also in part, is prohibited. This publication reflects the technical status at the time of printing.

Copyright by Conrad Electronic SE.

*2620278_V1_1123_en_ds 1111583243 I1/O1 en