

Crimp Fittings

Press-armaturen

Embouts sertis

Raccordi a graffare

Racores para presión

DK


24° Male, Light Duty

Außengewindeanschluss 24°, leichte Baureihe

Måle 24° serie L

Maschio metrico 24°, serie leggera

Macho fijo de 24°, serie ligera



Part Number	Part Number	Part Number	Thread T	Flange	Tube O.D.	ND	Hose Size	A	D	H	E Ø	HEX [1]	HEX [2]	K Ø
OTC Fitting	Skive Nipple	TTC Fitting						mm	mm	mm	mm			mm
1G5DK3	1S5DK3	1A5DK3	M12x1,5		6	5	-3	38,0	20,5		2,5	12		
1G5DK4	1S5DK4	1A5DK4	M12x1,5		6	6	-4	44,7	21,3		4,2	12		
1G6DK4	1S6DK4	1A6DK4	M14x1,5		8	6	-4	44,5	21,1		4,2	14		
1G8DK5	1S8DK5	1A8DK5	M16x1,5		10	8	-5	47,0	23,1		5,3	17		
1G8DK6	1S8DK6	1A8DK6	M16x1,5		10	10	-6	52,0	26,7		6,7	17		
1G10DK6	1S10DK6	1A10DK6	M18x1,5		12	10	-6	49,0	23,7		6,7	19		
1G10DK8	1S10DK8	1A10DK8	M18x1,5		12	12	-8	54,5	24,8		9,6	19		
1G12DK8	1S12DK8	1A12DK8	M22x1,5		15	12	-8	56,0	26,3		9,6	24		
1G16DK10	1S16DK10	1A16DK10	M26x1,5		18	16	-10	56,0	26,6		12,8	27		
1G20DK12	1S20DK12	1A20DK12	M30x2,0		22	19	-12	62,0	31,8		15,5	32		
1G25DK16	1S25DK16	1A25DK16	M36x2,0		28	25	-16	66,0	31,6		20,7	41		
1G32DK20	1S32DK20	1AP32DK20*	M45x2,0		35	31	-20	79,4	35,4		26,6	46		
		1AT32DK20**	M45x2,0		35	31	-20	79,4	35,4		26,6	46		
	1S40DK24	1A40DK24	M52x2,0		42	38	-24	85,0	38,7		32,0	55		

* 1-wire

** 2-wire

* 1-wire

** 2-wire

* 1-wire

** 2-wire

* 1-wire

** 2-wire

* 1-wire

** 2-wire

Specification subject to change without notice