




# 6010M, 6011M, 6012M, 6013M and 6091M Series Non-Relampable Oil-Tight Neon-LED Indicator Lights



Solid-state indicator lights complete with built-in current-limiting resistor and rectifier diode.

Mounting:  $\varnothing .380$ " (9.65mm) hole. Supplied with internal tooth lock washer and hex nut.

Wire Leads: Neon Models: No. 18 AWG (105°C) 4.4 (111.8)/4.8 (121.9) long, stripped .43 (10.9)/.57 (14.5)  
 LED Models: No. 22 AWG (105°C) 4.4 (111.8)/4.8 (121.9) long, stripped .43 (10.9)/.57 (14.5)

Lens: Polycarbonate

Bezel: Polished stainless steel.

Gasket: Buna-N

Housing: Black Nylon Zytel 101

cURus approval: Underwriters Laboratories (UL) File No. E20356

Lens Color	LED Solid State Indicator*		
	Model No. for 12V	Model No. for 24V	Incorporates LED
Red	6091M1-12V	6091M1-24V	4304H1
Green	6091M5-12V	6091M5-24V	4304H5
Yellow	6091M7-12V	6091M7-24V	4304H7
Internal Resistor (ohms)	390	1000	-
Wire Colors	1 White/1 Red	1 White/1 Red	1 White/1 Red

\* Note: Also incorporates IN4004 (400 P.I.V.) rectifier diode. Red lead positive.

Neon Indicator				
Lens Color	Part Number (105-125VAC)	Lamp used + Resistor	Part Number (208-250 VAC)	Lamp used + Resistor
Red	6010M1	C2A + Res. 30k $\Omega$	6011M1	C2A + Res. 100k $\Omega$
Amber	6010M3	C2A + Res. 30k $\Omega$	6011M3	C2A + Res. 100k $\Omega$
Green	6012M5	G2B + Res. 39k $\Omega$	6013M5	G2B + Res. 120k $\Omega$
Wire Color	Black		1 Black/1 Red	

## Compliance & Approvals

