



Custom Stripmaster Wire Stripper, #10 to #14 AWG w/ Grit Pad

Catalog # 45-173




Features


- Die-type blades
- For PVC and other misc. insulations
- For accuracy and precision to meet tough MIL-specs
- Strips solid or stranded wire
- For Type EE TEFLON® (1000V)
- *TEFLON® is a registered trademark of E.I. du Pont de Nemours and Company.*
- Die-type blades allow precision stripping
- Contains counterbored hole sized to insulation and inner stripping hole sized to conductor
- Die-types blades manufactured to assure accuracy and precision to meet tough MIL-Specs

Custom Stripmaster® and Custom Stripmaster® Lite Wire Strippers


- Strips 30 through 10 AWG solid or stranded wire
- Mil-spec die-type blades allow precision stripping
- Inner cutting hole sized to conductor and counter-bored holes sized to insulation
- Replaceable Grippers
- Optional short stop latch and transparent wire stop
- Cushioned, comfort grip handles
- Custom Stripmaster® Lite is 3/4's the size of Custom Stripmaster® Wire Stripper and strips 16 through 30 AWG solid or stranded wire
- Custom Stripmaster® Lite requires one-third less hand pressure for each strip actuation
- Engineering Service and made-to-order blades available. Contact factory for complete product and blade number listing.



Gripper pads hold the wire securely in a centerline relationship with the blade.



Die-type blades incorporate a counter-bored hole sized to the insulation and an inner cutting hole sized to the conductor. This varies depending on insulation type and thickness.



Custom Stripmaster® Wire Strippers and Die-Type Blades

Specifications — Cutting Hole Diameter Counterbore Diameter (Inches)											Stripper Cat. No.	Blade Only Cat. No.
Wire Size AWG												
30	28	26	24	22	20	18	16	14	12	10		
For Type E Teflon® (600V)												
								.076 .0935	.096 .113	.119 .136	45-176	L-5559
		.023 .039	.028 .043	.034 .052	.042 .0595	.052 .070	.061 .081				45-177	L-5560
.016 .032	.019 .035	.023 .039									45-178	L-5561
For Type EE Teflon® (1000V)												
								.076 .104	.096 .125	.119 .144	45-173	L-5562
		.023 .0465	.028 .055	.034 .0595	.042 .067	.052 .0785	.061 .089				45-174	L-5563
.016 .042	.019 .043	.023 .0465									45-175	L-5564
For Other Misc. Insulations												
								.076 .113	.0937 .138	.116 .154	45-170	L-5210
		.022 .052	.0292 .0595	.035 .0635	.042 .073	.052 .086	.062 .096				45-171	L-5211
.016 .037	.020 .040	.024 .043									45-172	L-5436
For Wire Wrap & Other Thin Insulated Wire												
.012 .020								Three identical holes			45-179	L-7625
.012 .019	.014 .023	.018 .025	.024 .033					Solid Wires			45-169	L-9300

Tolerances: Cutter Dia.: ± .001; Counter-bore Dia.: ± .002
 The 45-170 Series is a Custom Stripmaster® Wire Stripper frame without the short stop latch and wire stop.
 Teflon® is a registered trademark of E.I. du Pont de Nemours and Company.