
VEEDER-ROOT brand

Mechanical & Electric Counters

7790/7791 Series



Economical miniature totalizers. . . available in all popular mounts and operating voltages





The series 7790 is a non-reset totalizer that delivers excellent performance and reliability characteristics for a minimal price. The series 7791 includes a push-bar reset feature.

- Compact size
- Four standard mounting styles
- Five and six figure indication standard-high contrast white on black
- Capable of speeds up to 600 counts/minute
- Count coil can be continously energized
- Long service life
- Standard models for a broad range of AC and DC voltages
- UL recognized; CSA certification available

SPECIFICATIONS

Number of Figures: 7790: 6; 7791: 5

Figure Size: 0.156" high, 0.070" wide (4.0 mm X 1.8 mm)
Count Speed: 600 cpm (800 cpm available as special option)
Minimum Count Pulse Timing: 50 ms min. on time and off time

Continous Coil Energization: Voltage can be applied continously without

causing damage

Count Life: 10 million counts DC versions; 2 million counts AC versions,

under normal operating conditions at +77° F (+25° C)

Voltage: 24, 48, 115 VAC; 6, 12, 24 VDC

Voltage Tolerance: ±10% or 10 volts, whichever is limiting

Power Consumption: 5 VA AC, 1.5 VA DC

Operating Temperature Range: +32° F to +122° F (0 to 50° C)

Mounting: Base, panel, rear, and back of panel

Mounting Screws: Rear Mount: #4 (.112) 40 UNC-2B; Max. Screw Length

0.090; Max. torque 5.0 inch lbs. (0.565 Nm)


Back of Panel Mount: #4 (.112) 40 UNC-2B; Max. Screw Length 0.218;


Max. torque 7.5 inch lbs. (0.847 Nm)


Connections: #22 AWG leads, 10" (254 mm) long

Materials: Wheels, Verge and Pinions-acetal resin; Crystal-polycarbonate; Case and Panel Mounting Flange-polyphenylene oxide; Frame, Core, Armature and Base Mounting Flange-plated steel; Shafts-brass; Springsmusic wire

Net Weight: 3.2 oz. (90 grams)







DANAHER CONTROLS