

Pneumatic hose PUR

With fabric inlay



Execution:

- Shell made of ester-based polyurethane
- Polyester fibre fabric inlay
- Inner and outer layers made of polyester fibres
- Resistant to oil, solvents and non-aqueous solutions
- Straight version

Advantage:

- High elasticity, extremely flexible
- Long service life
- Excellent resistance to oil, solvents and non-aqueous solutions



Art. no.	75391 030
Brand	CEJN
Manufacturer Part Number	199581370
Inner hose diameter	9.5 mm
Outer diameter of hose	13.5 mm
Hose length	50 m
Min./max. temperature conditions	-30 to +60 °C
Max. operating pressure	12 bar
Burst pressure	48 bar
Material of hose	Polyurethane/polyester fibres
Colour	Blue
Gross Weight	5.130 kg
Product Group	7AI

EAN

7391390139733