

Balancer with load capacity of 3.0-21.0 kg

Type 7230, cable extraction 2000 mm

AUTOSTAT

Application:

Can be used for following tools and devices, e. g.: compressed air devices, electrical devices, paint spray guns, cable-binding pliers, nailing devices, flue gas swivelling arms, robot power supply line, welding pliers, packaging devices, etc.

Execution:

- Housing made of extremely shock-resistant special plastic
- Suspension via a freely turning and swivelling safety hook
- Infinitely adjustable load, via adjusting screw
- The load is attached via a safe screw snap hook
- Cable feed limitation is impact absorbing and adjustable
- Rope is infinitely variable in its length via a rope clamp
- If required, the cable can be replaced very easily
- Safety device: Fall arrester in line with DIN 15 112 included in scope of delivery, spring safety device, riveted special motive spring, cable drum, can be blocked (with integrated locking device), push clamp for securing the cable end
- Working area: Cable extraction: 2000 mm, ropes in special lengths available on request

Advantage:

- Effortless work



Art. no.	77000 600
Brand	AUTOSTAT
Manufacturer Part Number	77000600
Min. load-carrying capacity	4.5 kg
Max. load-carrying capacity	7 kg
Type	7230
With automatic locking	No
Max. cable pull-out length	2000 mm
Adjustable cord length	Yes
Material of cord	Steel
Wire cable diameter	3 mm
Replaceable cord	Yes
Cord in-feed restriction	Absorbs impacts, adjustable
Material of cable drum	Highly abrasion-proof plastic
Suspension type	Freely rotating and pivot safety hook
Load attachment	Screw Karabiner hook
Material of housing	Plastic
Housing width	180 mm
Housing thickness	130 mm
Colour of housing	Orange
Design	Standard
Height	520 mm
Spring design	Riveted special mainspring
With overrotation protection	No
Spring breakage protection	Yes
Number of springs	1 PCS
DIN	15 112
Gross Weight	3.805 kg
Product Group	772

EAN

4039247366583