

## Data Sheet | Item Number: 272-134/201-000


Power supply connector; without push-buttons; with snap-in mounting feet; with snap-in ground contact; 4-pole; 2,50 mm<sup>2</sup>; white

<https://www.wago.com/272-134/201-000>



Color: white

Similar to illustration



Dimensions in mm

### Electrical data

#### Ratings per IEC/EN

Ratings per	IEC/EN 60664-1
Rated voltage (III/2)	400 V
Rated impulse voltage (III/2)	4 kV
Rated current	18 A
Legend (ratings)	(III / 2) Δ Overvoltage category III / Pollution degree 2

### Connection data

Connection points	16
Total number of potentials	4
Number of connection types	1

#### Connection 1

Connection technology	PUSH WIRE®
Strip length	8 ... 9 mm / 0.31 ... 0.35 inches
Pole number	4

### Physical data

Width	38.5 mm / 1.516 inches
Height	19.5 mm / 0.767 inches
Depth	24.5 mm / 0.965 inches

### Material Data

Note (material data)

[Information on material specifications can be found here](#)

Color	white
Material group	I
Insulation material	Polyamide (PA66)
Flammability class per UL94	V0
Fire load	0.216 MJ
Weight	13.7 g

Commercial data	
Product Group	8 (Misc. Chassis Mount Blocks)
eCl@ss 10.0	27-14-11-04
eCl@ss 9.0	27-14-11-04
ETIM 8.0	EC000446
ETIM 7.0	EC000446
PU (SPU)	500 pcs
Packaging type	Bag
Country of origin	DE
GTIN	4044918430074
Customs tariff number	85369010000

## Approvals / Certificates

### General approvals



Approval	Standard	Certificate Name
CSA DEKRA Certification B.V.	C22.2 No. 158	70048844

## Downloads

### Environmental Product Compliance

Compliance Search	
Environmental Product Compliance 272-134/201-000	<a href="#">↓</a>

## Documentation

Additional Information			
Technical Section	03.04.2019	pdf 1949.09 KB	<a href="#">↓</a>

## 1 Compatible Products

### 1.1 Optional Accessories

#### 1.1.1 Tool

### 1.1.1.1 Assembly tool



**Item No.: 249-100**

Operating tool; for terminal blocks with snap-in ground contact

### 1.1.1.2 Operating tool



**Item No.: 271-120**

Push-button; white