

3 Pin Pluggable
Screw Connection
Field Assembly

Connectors

WPF-WPM-WPP Series


3 pin
300 VAC
25A


IP68
10 m. / 60 min.



WPM-0300M25

3 Pin Male Cable Type




WPF-0300M25

3 Pin Female Cable Type



WPP-0300M25

3 Pin Male Panel Type



GONTUANA[®]
Waterproof Connector Series

Technical Specifications



Number of Poles
Voltage Rating
Current Rating
Cable Cross Section Area
Durability Voltage
Insulation Structure
Contact Resistance
Min Wire Size OD
Max Wire Size OD
Temperature Rating
IP Class
Mold Material
Contact/Terminal Material
Seal Material

Product Codes


WPM-0300M25
WPF-0300M25
WPP-0300M25

3
300VAC max.
25A max.
0,5mm² ~ 2,5mm²
3000VAC@60s.
500 MΩ at 500VDC
30 mΩ max.
5,5mm
8,5mm
-40°C ~ +85°C
IP68 (10m/60min.)
PA6
Nickel-Plated Brass
Silicone

WPP-0300M25



WPF-0300M25



WPM-0300M25

