

**PAC  
PAC-UNIV-HE50-HE50-3M**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



Similar to illustration

Cable preconfeccionado cable plano según IEC-603/  
DIN41651.

- Cable plano - cable plano
- Cable plano - punteras

**General ordering data**

Type	PAC-UNIV-HE50-HE50-3M
Order No.	<a href="#">1349720030</a>
Version	Pre-assembled cable, PAC
GTIN (EAN)	4032248217632
Qty.	1 pc(s).

**PAC**  
**PAC-UNIV-HE50-HE50-3M**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**
**Dimensions and weights**

Net weight	512.7 g
------------	---------

**Temperatures**

Operating temperature, max.	50 °C	Operating temperature, min.	-10 °C
Storage temperature, max.	60 °C	Storage temperature, min.	-10 °C
Operating temperature	-10...50 °C	Storage temperature	-10...60 °C

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
------------	----------------

**General Data**

Connector PLC side	HE10 50 P	Interface connector	HE10 50 P
Number of poles, min.	50-pole	Outer diameter	13.4 ± 1 mm
Cable	Cable LiYY	Cable length	3 m
Material	PVC	Wire cross-section	0.14 mm <sup>2</sup>

**Electrical Data**

Rated voltage (text)	≤ 60 V DC ≤ 25 V AC	Permissible current strength per path, max.	1 A
Total current, max.	3 A	Resistance	≤ 150mΩ/m

**Classifications**

ETIM 5.0	EC000237	ETIM 6.0	EC000237
eClass 6.2	27-24-92-05	eClass 7.1	27-24-92-05
eClass 8.1	27-24-92-05	eClass 9.0	27-24-22-20
eClass 9.1	27-24-22-20		

**Approvals**

ROHS	Conform
------	---------