

product type designation

product description



MV500 E-focus C-mount lens, 25 mm

C mount lens, 25 mm focal distance with electronic focus, set aperture 8

E-focus lens 25 mm Only for MV500 devices (MLFB: 6GF3540-0CD10, -0GE10, 6GF3550-0CD10, -0GE10; 6GF3560-0LE10, -HE10; EDMUND lens with liquid lens focal length 25 mm; focus electrically adjustable; fixed aperture; scope of delivery: lens and cable .

suitability for use	Swappable lens with C-mount connection
suitability for operation	lens for MV500
electrical data	
number of electrical connections	1
type of electrical connection	Internal plug-in connector
mechanical data	
color	black
ambient conditions	
ambient temperature	
• during operation	0 ... 50 °C
• during storage	-30 ... +70 °C
• during transport	-30 ... +70 °C
design, dimensions and weights	
height	28 mm
diameter	34.2 mm
further information / internet links	
internet link	
• to website: TIA Selection Tool	http://www.siemens.com/tia-selection-tool
• to website: Industrial communication	http://www.siemens.com/codereader
• to website: Industry Mall	https://mall.industry.siemens.com
• to website: Information and Download Center	http://www.siemens.com/industry/infocenter
• to website: Selection guide for cables and connectors	https://sie.ag/2QdlxcP
• to website: Image database	http://automation.siemens.com/bilddb
• to website: CAx-Download-Manager	http://www.siemens.com/cax
• to website: Industry Online Support	https://support.industry.siemens.com

last modified:

5/28/2023 