

Euromas Aluminium / Euromas F05

Enclosure, aluminium



A 105

Order no.: 01105000

* = Available on request.

Characteristics

Colour of enclosure group

Grey, similar to RAL 7001

Protection class

IP 66

Enclosure Material

G Al Si 12, PU foamed seal

For details see Technical Information

Scope of delivery

Lid and base, lid screws made of V2A, earthing screw

Note

On the A 198, because of the wall-mounting drill holes inside the sealed lip, expert sealing of the wall-mounting is necessary to achieve protection class IP 66.


G = design with transparent lid (PC)

Dimensions

Dimensions

75 x 80 x 57 mm

Product drawing



Important!

To compensate for pressure when temperatures change and cause moisture in the enclosure, we recommend that you use a pressure compensation element.

» Additional information

20.02.2020

Technical documentation / Downloads

Technical drawings

3D product data in STEP format: Registration necessary
Product drawing in PDF format: 01105000 A-105.pdf (72.1 KB)
Product drawing in DXF format: 01105000 A-105.dxf (492.9 KB)
Drawing for mechanical processing: 01105000 A-105-G.dxf (298.9 KB)

Milling contours are shown here as a DXF file. (Sub D, USB, HDMI, cable glands, ...)

Works Test Certificates

682 WPZ-Euomas-Aluminium DE.pdf (163.7 KB)
682 WPZ-Euomas-Aluminium EN.pdf (143.7 KB)

Product information

Euomas Aluminium F05 GB.pdf (1.8 MB)

Matching accessories



Capstan-headed screws, sealable

21007915 KP

For A 100-118



Allen cheese-head screw for lid

21007920 IS

For A 101-118



DIN rails DIN EN 60715 TH 15, galvanised steel

21002800* TS 15

For A 105, P 305, P 326, PK 105



Set of hinges

21007800 SCHD



Mounting panels for PK 105 - 115, galvanised sheet steel

21001100 M

For A 105, PK 105