

Model No.: **GP14AUP**




NO MERCURY ADDED	
<b>Description</b>	: Mercury & Cadmium Free Alkaline Manganese Battery, C Size
<b>Chemical System</b>	: Alkaline Manganese
<b>Nominal Voltage</b>	: 1.5 Volts
<b>Nominal Dimensions</b>	: $\phi 26.2$ mm x 50.0 mm
<b>Terminals</b>	: Protruded positive (+) and flat negative (-) contacts
<b>Jacket</b>	: Foil jacket
<b>Applications</b>	: All electronic devices, e.g. transistor radios, cassette recorders, toys, alarm clocks, lighting & torches, portable fans.
<b>Shelf Life</b>	: 10 years at 20°C in a well ventilated area
<b>Average Weight</b>	: 60g

### Cross References:

GP	JIS	IEC	Eveready	Duracell	Varta
14AU	LR14	LR14	E39	MN1400	4014

### Typical Service Life:

Discharge Resistance	Discharge Condition	End Point Voltage	Service Life
3.9 Ohms	24 Hrs/Day	0.9V	18.5 Hrs



Unit : mm

The information (subject to change without prior notice) contained in this document is for reference only and should not be used as a basis for product guarantee or warranty. For applications other than those described here, please consult your nearest GP Sales and Marketing Office or Distributors.