

# LASER DISTANCE MEASURER

**Water Resistant, Dust Resistant, Multi-Measurements**

- Easily and quickly measuring.
- LCD display with backlight allows for data reading in dark areas.
- Easy measurement with one touch.
- Integrated multi-measuring and calculation functions.
- Auto laser off and auto power off function.
- Comply with IP54 rated as dust and water resistant.



**NT-6540**  
**40M**  
measurement







**NT-6560**  
**60M**  
measurement

**40M**

Ideal for measuring room dimension for cooling, home layout, cable linear length, align large fixtures, house maintenance

**60M**

Ideal for measuring office layout, check tank level, cell tower setting, hole depth, electrical safety area



SPECIFICATION	NT-6540	NT-6560
Display	LCD display (2 lines)	LCD display (4 lines)
Backlight	Y	Y
Measuring range	0.1-40M	0.2-60M
Accuracy	±2mm	±2mm
Unit selection	m/ft/in/ft+in	m/ft/in/ft+in
Continuous measurement	Y	Y
MAX/MIN measurement	N	Y
Area calculations	Y	Y
Volume calculations	N	Y
Memory	10 records	20 records
Buzzer indication	Y	Y
Pythagorean 1	Y	Y
Pythagorean 2	N	Y
Add/Subtraction	N	Y
Auto laser off	After 20 second	After 30 second
Auto power off	After 3 min	
Laser Class	Class II	Class II
Laser type	650 nm, < 1mW	635 nm, < 1mW
Certificate	IP54	
Operating Temperature	0°C to +40°C (32°F to 104°F)	
Storage Temperature	-10 °C to +60°C (14°F to 140°F)	
Battery type	Type AAA 2 x 1.5V	
Battery life	Up to 5000 time(only for reference)	
Dimension	100x43x28mm	120x50x30mm
Weight(not include batteries)	60g	100g
Individual Packing	Double Blister Card	Double Blister Card

Picture for reference only. Please check with distributor for exact offers. All specifications are subject to change without notice.