



### Model Number


**V1S-W-PG9**

Male cordset, M12, 4-pin, field attachable

### Features

- Metal locking

## Dimensions



## Technical data

### General specifications

Number of pins	4
Connection 1	Male connector
Construction type 1	right angle
Threading 1	M12
UL File Number	E363587

### Electrical specifications

Operating voltage	$U_B$	max. 250 V AC/DC
Operating current		max. 4 A
Volume resistance		< 8 m $\Omega$

### Ambient conditions

Ambient temperature	-25 ... 85 °C (-13 ... 185 °F)
Pollution Degree	3

### Mechanical specifications

Degree of protection	IP67
Connection	1 x M12 right-angled connector Screw terminals for max. 0.75 mm <sup>2</sup> PG9 cable gland
Material	
Contacts	CuZn
Contact surface	CuSnZn
Connector	CuZn
Body	PA
Cable	
Sheath diameter	6 ... 8 mm

### Compliance with standards and directives

Standard conformity	
Degree of protection	EN 60529:2000

## Electrical connection

