

Product type designation

PROFIBUS bus terminal 12M

12M BUS TERMINAL FOR PROFIBUS, TRANSMISSION RATE 9.6 KBIT/S TO 12 MBIT/S, CONNECTING CABLE 1.5 M



Electrical data	
Transfer rate / with PROFIBUS	9.6 kbit/s ... 12 Mbit/s
Interfaces	
Number of electrical connections	2
<ul style="list-style-type: none"> for PROFIBUS cables 	
Type of electrical connection	Screw terminals
<ul style="list-style-type: none"> for PROFIBUS cables 	
Mechanical data	
Material / of the enclosure	plastic
Design, dimensions and weight	
Width	50 mm
Height	138 mm
Depth	53 mm
Net weight	360 g
Mounting type	Yes
<ul style="list-style-type: none"> 35 mm DIN rail mounting 	
Standards, specifications, approvals	
Certificate of suitability	Yes
<ul style="list-style-type: none"> UL approval 	
Further Information / Internet Links	
Internet-Link	

- to website: Selector SIMATIC NET SELECTION TOOL
- to website: Industrial communication
- to website: Industry Mall
- to website: Information and Download Center
- to website: Image database
- to website: CAx Download Manager
- to website: Industry Online Support

last modified:

<http://www.siemens.com/snst>

<http://www.siemens.com/simatic-net>

<https://mall.industry.siemens.com>

<http://www.siemens.com/automation/net/catalog>

<http://automation.siemens.com/bilddb>

<http://www.siemens.com/cax>

<https://support.industry.siemens.com>

09.03.2015