



EXHAUST FILTERS MOUNTING CUT OUT 223X223  
MM RAL 7035 DEGREE OF PROTECTION IP 54  
ACCURACY CLASS 3

Figure similar

Model		
product brand name		SIVACON
Product designation		outlet filter
Type of ventilation		ventilation
Fan design / Insertable fan		No
Design of the product / EMC version		No
General technical data		
Cutout width	mm	223
Cutout height	mm	223
Operating temperature / minimum	°C	-20
Protection class		
Protection class IP		IP54
Appearance		
Color		RAL 7035
Product details		
Product component / Fan		No
Mechanical Design		
Height	mm	250
Width	mm	250
Depth	mm	37
Installation location		Control cabinet...panels, door
Mounting type		snap-on mounting
Mounting type		

- 19-inch installation
- wall mounting

No
Yes
plastic

**Material**

**Certificates**

**Equipment marking**

- acc. to DIN EN 61346-2
- acc. to DIN EN 81346-2

V
V

**General Product Approval**



**Further information**

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/8MR64005GV45>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<http://support.automation.siemens.com/WW/view/en/8MR64005GV45/all>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mfb=8MR64005GV45](http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=8MR64005GV45)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://ausschreibungstexte.siemens.com/tiplv>

last modified:

11.03.2015