



Cut



Medium Duty

Cost effective solution for medium weight applications requiring high level of cut performance in dry or slightly oily environments

- Made of a seamless liner, palm dipped into foam nitrile coating
- ANSI cut level A3 and EN ISO 13997 rated level C provide a good level of cut resistance.
- The nitrile coating delivers very good performance in terms of abrasion resistance and grip.
- The choice for medium to heavy duty applications that require abrasion, grip and cut protection
- The best alternative against heavy duty leather and polyurethane palm dipped cut resistant knitted gloves.



Industries

- Automotive
- Construction
- Glass manufacturing
- Machinery and Equipment
- Metal fabrication

Applications

- General maintenance
- Hardware assembly
- Machining / Stamping / Cutting
- Molding
- Plastic injections
- Raw material handling
- Seat and frame build

Key Features

- High durability Nitrile foam coating
- Excellent comfort and dexterity
- High level of cut performance EN ISO level C cut performance (ANSI Level 3)
- Excellent abrasion resistance
- In compliance with the standards

EN420 (General requirements) and

EN388 (Mechanical hazards)

- Breathable liner that allow very high level of comfort for end users
- Good level of grip in dry and slightly oily environments

Vulcanization Chemical Accelerators

- Natural rubber proteins (in knitwrist elastic)
- Zinc Diethyldithiocarbamate

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Performance Standards & Regulatory Compliance

REACH Compliant



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COLOR	PACKAGE
EDGE [®] 48-706	Finishing: Palm Coated Coating Material: Foam Nitrile Liner Material: HPPE, Fiber glass, Nylon, Polyester, Spandex Cuff Style: Knitwrist	13	6, 7, 8, 9, 10, 11	220-270 mm; 8.66-10.63 inches	Black	<ul style="list-style-type: none"> • 12 pairs/bag; 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
 Riverside Business Park
 Blvd International, 55
 1070 Brussels, Belgium
 T: +32 (0) 2 528 74 00
 F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
 111 Wood Avenue South,
 Suite 210
 Iselin, NJ 08830, USA
 T: +1 800 800 0444
 F: +1 800 800 0445

Australia

Ansell Limited
 Level 3,678 Victoria Street,
 Richmond, Vic, 3121
 Australia
 T: +61 1800 337 041
 F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
 (Malaysia) Sdn Bhd
 Prima 6, Prima Avenue
 Block 3512, Jaijan Teknokrat 6
 T: +603 8310 6688
 F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
 Blvd. Bernardo Quintana No. 7001-C,
 Q7001 Torre II,
 Suites 1304, 1305 y 1306,
 Col. Centro Sur, c.p. 76079
 Queretaro, Qro. Mexico
 T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
 105 Lauder
 Cowansville, QC J2K 2K8
 Canada
 T: +1 800 363 8340
 F: +1 800 267 3551

Ansell, [®] and [™] are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2022 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.