


Part number

CX 25 IM



Brief description:

male insert, 25 poles, crimp connections, 4A 50V, 3, for 5A male contacts, 1 module, modular units series MIXO

Product description		Approvals / Standards	
Model	male insert	Reference standard	EN 61984:2009-06
Version	Crimp connection	Quality mark	 DNV GL, BV, EAC
Product type	for 5A male contacts	Conformity	Not applicable
Family	MIXO series, customizable inserts	General ordering information	
Size	1 module	EAN13 code	8015747148320
N. of poles	25 poles	Tariff number	85369095
Technical data		Packaging Information	
Current	4 A (A.C. and D.C.)	Packaging length	180,00 mm
Voltage	50 V	Packaging height	130,00 mm
Pollution degree	3	Packaging width	150,00 mm
Operating temperature range (min, max)	-40°C ... +125°C	Packaging weight	2,00 kg
IP degree of protection	IP20 without enclosure, IP65/IP66/IP68/IP69 with enclosure	Packaging volume	3,51 dm ³
Further technical details		Packaging description	Carton box
Characteristics according to EN 61984	5A 50V 10A 3	Packaging quantity	60 Pcs
Insulation resistance	≥ 10 GΩ	Packaging EAN code	8015747221368
Rated voltage according to UL/CSA	50V	Sub-packaging length	35,00 mm
UL 94 flammability rating	V-0	Sub-packaging height	40,00 mm
Weight	9,00 g	Sub-packaging width	155,00 mm
		Sub-packaging weight	0,33 kg
		Sub-packaging volume	0,22 dm ³
		Sub-packaging description	Carton tray
		Sub-packaging quantity	10 Pcs
		Sub-packaging EAN barcode	8015747148344

Part number

CX 25 IM



Notes

Inserts CX 25 IF/M

- characteristics according to EN 61984:
4A 50V 0.8kV 3
4A 160V 2.5kV 2
- insulation resistance: > 10 GOhm
- ambient temperature limit: -40 °C ... +125 °C
- are made of self-extinguishing thermoplastic resin
UL 94 V0
- mechanical life: > 500 cycles
- for crimp contacts CI series using:
CIPZ D crimping tool
CITP D turret head
CIES insertion / removal tool
- we recommend the use of CRF / CRM code pins
- 1 frame slot

the modular inserts must be installed in suitable frames which in turn are installed in traditional housings or COB panel support

Part number
CIMD 0.2



Brief description:

CI male contacts, 5A, gold plated, 0,08 mmq - 0,21 mmq, AWG 28 - 24

Product description

Model	male contacts
Version	Crimp contacts CLASS series
Series	CI 4A contacts
Family	crimp contacts
N. of poles	1 pole

Technical data

Current	5 A
Wire cross-section	0,08 mm ² - 0,21 mm ²
AWG size	28 - 24
Contact type	gold plated

Further technical details

Conductors stripping length	4 mm
Weight	0,22 g

Approvals / Standards

Quality mark	
Conformity	Not applicable

General ordering information

EAN13 code	8015747176699
Tariff number	85369095

Packaging Information

Packaging weight	0,29 kg
Packaging description	Carton box
Packaging quantity	1000 Pcs
Packaging EAN code	8015747258623
Sub-packaging length	75,00 mm
Sub-packaging height	89,00 mm
Sub-packaging width	110,00 mm
Sub-packaging volume	0,73 dm ³
Sub-packaging description	Plastic bag
Sub-packaging quantity	25 Pcs
Sub-packaging EAN barcode	8015747044004

Part number

CIMD 0.2



Catalogue drawings

CIF CIM

