

Male headers soldering technique

□ 0.635 mm, standard

| | | | | | | | |
|-------------------------|--|------|-------|---|-----------|------|-------|
| | | | | | | | |
| art. no. | dim. [mm] | | | art. no. | dim. [mm] | | |
| | A | B | C | | A | B | C |
| SL 11 112 ... | 11.20 | 3.00 | 5.40 | SL 1 025 ... | 11.20 | 2.60 | 5.80 |
| SL 11 124 ... | 12.40 | 3.00 | 6.60 | SL 1 053 ... | 13.90 | 5.80 | 5.30 |
| SL 11 139 ... | 13.90 | 3.00 | 8.10 | SL 1 078 ... | 16.40 | 5.80 | 7.80 |
| SL 11 164 ... | 16.40 | 3.00 | 10.60 | SL 1 104 ... | 19.00 | 5.80 | 10.40 |
| SL 11 190 ... | 19.00 | 3.00 | 13.20 | SL 1 128 ... | 21.40 | 5.80 | 12.80 |
| SL 11 214 ... | 21.40 | 3.00 | 15.60 | SL 1 154 ... | 24.00 | 5.80 | 15.40 |
| SL 11 240 ... | 24.00 | 3.00 | 18.20 | SL 1 179 ... | 26.50 | 5.80 | 17.90 |
| SL 11 265 ... | 26.50 | 3.00 | 20.70 | SL 1 230 ... | 31.60 | 5.80 | 23.00 |
| SL 11 316 ... | 31.60 | 3.00 | 25.80 | | | | |
| | | | | | | | |
| art. no. | dim. [mm] | | | art. no. | dim. [mm] | | |
| | A | B | C | | A | B | C |
| SL 22 112 ... | 11.20 | 3.00 | 5.40 | SL 2 025 ... | 11.20 | 2.60 | 5.80 |
| SL 22 124 ... | 12.40 | 3.00 | 6.60 | SL 2 053 ... | 13.90 | 5.80 | 5.30 |
| SL 22 139 ... | 13.90 | 3.00 | 8.10 | SL 2 078 ... | 16.40 | 5.80 | 7.80 |
| SL 22 164 ... | 16.40 | 3.00 | 10.60 | SL 2 104 ... | 19.00 | 5.80 | 10.40 |
| SL 22 190 ... | 19.00 | 3.00 | 13.20 | SL 2 128 ... | 21.40 | 5.80 | 12.80 |
| SL 22 214 ... | 21.40 | 3.00 | 15.60 | SL 2 154 ... | 24.00 | 5.80 | 15.40 |
| SL 22 240 ... | 24.00 | 3.00 | 18.20 | SL 2 179 ... | 26.50 | 5.80 | 17.90 |
| SL 22 265 ... | 26.50 | 3.00 | 20.70 | SL 2 230 ... | 31.60 | 5.80 | 23.00 |
| SL 22 316 ... | 31.60 | 3.00 | 25.80 | | | | |
| please indicate: | ... no. of contacts one row 1-36 two rows 2-72 | | | ... surface S = selective gold-plated G = gold-plated Z = tin-plated | | | |

Every pin length is available on request.

PC connector design DIL
Female headers 2.54 solder
Technical data
Fem. head. 2.54 solder, put through

→ H 2
→ G 27
→ G 73 - 76
→ G 28

Female headers 2.54 SMD
Special male & female headers
High-prec. fem. headers 2.54 sold.
Bar magazine

→ G 41 - 44
→ G 18
→ G 30 - 33
→ G 20 - 21