

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1731090647](#)  
**Status:** **Active**  
**Overview:** [FCT D-Sub Connectors](#)  
**Description:** FCT Standard-Density D-Sub Connector, Female, Straight, Solder Cup, Gold over Nickel Phosphorus Plating, 500 Mating Cycles, 25 Circuits

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

**General**

|                    |                                      |
|--------------------|--------------------------------------|
| Product Family     | D-Sub Products                       |
| Series             | <a href="#">173109</a>               |
| Datasheet Order No | 987651-8284                          |
| Exclude SD Check   | Yes                                  |
| IP Rating          | IP20                                 |
| Overview           | <a href="#">FCT D-Sub Connectors</a> |
| Product Category   | D-Sub Connector                      |
| Product Name       | FCT Products                         |
| Type               | Standard Density                     |
| UPC                | 191128756693                         |

**Physical**


|                                |                             |
|--------------------------------|-----------------------------|
| Circuits (Loaded)              | 25                          |
| Circuits (maximum)             | 25                          |
| Color - Resin                  | White                       |
| Durability (mating cycles max) | 500                         |
| Gender                         | Female                      |
| Material - Contact             | Copper Alloy                |
| Material - Resin               | PBT                         |
| Material - Shell               | Steel                       |
| Net Weight                     | 12.400/g                    |
| Number of Rows                 | 2                           |
| Orientation                    | Straight                    |
| PCB Locator                    | No                          |
| PCB Retention                  | None                        |
| Packaging Type                 | Carton                      |
| Panel Mount                    | Rear                        |
| Panel Mount Method             | Flange                      |
| Pitch - Mating Interface       | 2.84mm                      |
| Pitch - Termination Interface  | 2.84mm                      |
| Plating - Contact              | Gold over Nickel Phosphorus |
| Plating - Shell                | Tin                         |
| Polarized to Mating Part       | Yes                         |
| Ports                          | 1                           |
| Shielded                       | Yes                         |
| Temperature Range - Operating  | -55° to +125°C              |
| Termination Style              | Solder Cup                  |
| Waterproof / Dustproof         | No                          |
| Waterproof / Dustproof Type    | IP20                        |
| Wire Size AWG                  | 20                          |

**Electrical**

|                               |      |
|-------------------------------|------|
| Current - Maximum per Contact | 7.5A |
|-------------------------------|------|

**Material Info**

|                    |          |
|--------------------|----------|
| Engineering Number | F25S0G1A |
|--------------------|----------|



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[173109 Series](#)

**Mates With**

FCT Standard-Density D-Sub, Size 3, 25 Position, Plug

This document was generated on 06/26/2019

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**