

Product information

74 91 250

High Leverage Centre Cutter



- With integrated forged axle for heavy duty
- With precision cutting edges for soft, hard and piano wire
- Cuts thick wires with less effort than other diagonal cutters of the same length
- Centric precision cutting edges
- High cutting performance with minimum effort due to optimum coordination of the cutting edge angle and transmission ratio
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 62 HRC
- Chrome vanadium heavy-duty steel, forged, multi stage oil-hardened



General

Article No.	74 91 250
EAN	4003773034070
Pliers	black atramentized
Head	polished
Handles	plastic coated
Weight	395 g
Dimensions	250 x 52 x 16 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Cutting capacities soft wire (diameter)	Ø 5 mm
Cutting capacities medium hard wire (diameter)	Ø 5.0 mm
Cutting capacities hard wire (diameter)	Ø 3.8 mm
Cutting capacities piano wire (diameter)	Ø 3.5 mm

technical change and errors excepted

