

## Product information

# 87 26 250 T

### KNIPEX Cobra® VDE

High-Tech Water Pump Pliers, insulated

DIN ISO 8976 IEC 60900 DIN EN 60900



⚡ 1000 V 



- Pliers with integrated, insulated tether attachment point for a tool tether
- Adjustment by sliding one jaw directly on to the workpiece: fast, reliable and comfortable handling
- Fine adjustment: allows optimum adjustment to differently sized workpieces and comfortable handle position
- Good access to the workpiece due to slim size of head and joint area
- Self-locking on pipes and nuts: no slipping on the workpiece and low handforce required
- Gripping surfaces with special hardened teeth, teeth hardness approx. 61 HRC: high wear resistance and stable gripping
- Box-joint design for high stability due to double guide
- Pinch guard prevents operators' fingers being pinched
- Chrome vanadium electric steel, forged, multi stage oil-hardened

#### General

Article No.	87 26 250 T
EAN	4003773081517
Pliers	chrome-plated
Head	chrome-plated
Handles	insulated with multi-component grips, VDE-tested with integrated insulated tether attachment point for a tool tether
Weight	400 g
Dimensions	250 x 72 x 28 mm
Standard	DIN ISO 8976 DIN EN 60900 IEC 60900
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

#### Technical details

Adjustment positions	24
Capacities for pipes (diameter)	Ø 2 Inch
Capacities for nuts	46 mm
Capacity for pipes, inches (diameter)	Ø 50 mm
Drop Protection System	yes

*technical change and errors excepted*