

**Chip Metalfilm - Resistors 0603 & 0402****SBR-03****(6 Flap FL24/10) 144 Values / 6.480 Pieces)****Chip Resistors Thin Film****Type/Brand:** MCT0603 / Vishay Beschlag**Wattage:** 0,063W**Tolerance:** ±1%**TC:** 50ppm/°C

1 Value OR00

143 Values IEC-Series E24 (±1%) from 10R to 10M (Exception: 9M1)

**Binder: CCO-70 (Dimensions: 318x260x75)****Chip Package No.**

	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15
1	10R0	23R7	56R2	133R	316R	750R	1K78	4K22	10K0	23K7	56K2	133K	316K	750K	3M16
2	10R5	24R9	59R0	140R	332R	787R	1K87	4K42	10K5	24K9	59K0	140K	332K	787K	3M48
3	11R0	26R1	61R9	147R	348R	825R	1K96	4K64	11K0	26K1	61K9	147K	348K	825K	3M83
4	11R5	27R4	64R9	154R	365R	866R	2K05	4K87	11K5	27K4	64K9	154K	365K	866K	4M22
5	12R1	28R7	68R1	162R	383R	909R	2K15	5K11	12K1	28K7	68K1	162K	383K	909K	4M64
6	12R7	30R1	71R5	169R	402R	953R	2K26	5K36	12K7	30K1	71K5	169K	402K	953K	5M11
7	13R3	31R6	75R0	178R	422R	1K00	2K37	5K62	13K3	31K6	75K0	178K	422K	1M00	5M62
8	14R0	33R2	78R7	187R	442R	1K05	2K49	5K90	14K0	33K2	78K7	187K	442K	1M10	6M19
9	14R7	34R8	82R5	196R	464R	1K10	2K61	6K19	14K7	34K8	82K5	196K	464K	1M21	6M81
10	15R4	36R5	86R6	205R	487R	1K15	2K74	6K49	15K4	36K5	86K6	205K	487K	1M33	7M50
11	16R2	38R3	90R9	215R	511R	1K21	2K87	6K81	16K2	38K3	90K9	215K	511K	1M47	8M25
12	16R9	40R2	95R3	226R	536R	1K27	3K01	7K15	16K9	40K2	95K3	226K	536K	1M62	9M09
13	17R8	42R2	100R	237R	562R	1K33	3K16	7K50	17K8	42K2	100K	237K	562K	1M78	10M
14	18R7	44R2	105R	249R	590R	1K40	3K32	7K87	18K7	44K2	105K	249K	590K	1M96	
15	19R6	46R4	110R	261R	619R	1K47	3K48	8K25	19K6	46K4	110K	261K	619K	2M15	
16	20R5	48R7	115R	274R	649R	1K54	3K65	8K66	20K5	48K7	115K	274K	649K	2M37	
17	21R5	51R1	121R	287R	681R	1K62	3K83	9K09	21K5	51K1	121K	287K	681K	2M61	
18	22R6	53R6	127R	301R	715R	1K69	4K02	9K53	22K6	53K6	127K	301K	715K	2M87	0R0
	1%	1%	1%	1%	1%	1%	1%	1%	1%	1%	1%	1%	1%	1%	1%

REV: 30.10.2013

**SBR-0301****(1 Flap FL24/10) 24 Values / 1.080 Pieces**  
**Chip Resistors Thin Film****Type/Brand:** MCT 0603 / BEYSCHLAG**Wattage:** 0,063W**Tolerance:** ±1%**TC:** 50ppm/°C**Values-Quantities Selection:**

1R0	45x	1R1	45x	1R2	45x	1R3	45x	1R5	45x	1R6	45x
1R8	45x	2R0	45x	2R2	45x	2R4	45x	2R7	45x	3R0	45x
3R3	45x	3R6	45x	3R9	45x	4R3	45x	4R7	45x	5R1	45x
5R6	45x	6R2	45x	6R8	45x	7R5	45x	8R2	45x	9R1	45x

REV: 30.10.2013

**SMR-06**

**(2 Flap FL24/10) 48 Values / 8.550 Pieces**  
**Thickfilm-Chipresistors**

**Type/Brand:** RTT02 (RTR02) Fab. Ralec or alternative

**Tolerance:** ±1%

**TC:** 100ppm/°C

**Value Range:** 10 Ohm - 6,8 KOhm (E12) 10 KOhm - 1 MOhm (E6)

**Size:** 0402 (1,0x0,5x0,25mm)

**Values-Quantities-Selection:**

10	207x	12	115x	15	207x	18	115x	22	207x	27	115x
33	207x	39	115x	47	207x	56	115x	68	207x	82	115x
100	207x	120	115x	150	207x	180	115x	220	207x	270	115x
330	207x	390	115x	470	207x	560	115x	680	207x	820	115x
1K	207x	1K2	115x	1K5	207x	1K8	115x	2K2	207x	2K7	115x
3K3	207x	3K9	115x	4K7	207x	5K6	115x	6K8	207x	10K	207x
15K	207x	22K	207x	33K	207x	47K	207x	68K	207x	100K	207x
150K	207x	220K	207x	330K	207x	470K	207x	680K	207x	1M0	207x

**SMR-07**

**Chip Resistor**  
**(7 Flaps FL24/10) 168 Values / 15.120 Pieces**

**Type/Brand:** RTT02 (RTR02) Fab. Ralec or alternative

**Wattage:** 0,063 W

**Tolerance:** ±1%

**TK:** 100ppm/°C

**Size:** 0402

**Quantity:** 90 Pieces / Value

**Values:** 1 Ohm -10M Ohm (E24) (except 9M09)

**Binder:** 1 x CCO-70 (Dimension 318x260x70)

REV: 30.10.2013

**SMR-09** *Type discontinued, delivery as long as stocks last*

**Chip Resistor**  
**(11 Flaps FL24/10) 263 Values / 15.254 Pieces**

**Type/Brand:** RK73H (C0402) / KOA or Alternative

**Wattage:** 0,063 W

**Tolerance:** ±1%

**TK:** 100ppm/°C

**Size:** 0402

**Quantity:** 58 Pieces / Value

**Values:** 10 Ohm -10M Ohm (Ergänzung zur E-96) (except 7M87)

**Binder:** 2 x CCO-70 (Dimension 318x260x70)

**This assortment results in the E-96 serie in addition of the SMR-08**

**SMR-61**

**Chip Resistor**  
**((5 Flaps FL24/10) 120 Values / 18.100 Pieces**

**Type/Brand:** RTT03 / Fab. RALEC

**Wattage:** 0,1W

**Tolerance:** ±1%

**TK:** 100ppm/°C

**Size:** 0603

**Values:** 10 Ohm -1M Ohm (E24) (except 910K)

**Binder:** 1 x CCO-70 (Dimensions: 318x260x70)

REV: 30.10.2013