

**Manufacturer:** VOLEX

**Manufacturer Part No:** X-428796A



### Product Information

---

• Cable Length - Imperial:	8.2ft
• Cable Length - Metric:	2.5m
• Connector Type A:	Mains Plug, Aus
• Connector Type B:	IEC 60320 C13
• Jacket Colour:	Black
• SVHC:	No SVHC (16-Jun-2014)
• Voltage Rating:	250V

Non-rewireable lead for use in Australia, New Zealand, Fiji, Papua New Guinea and ROC. The plug complies with **AS3112-1990** and **NZSS198-1967**. Two and a half metres of 1.0mm<sup>2</sup> cable to harmonised code **H05VV-F** interconnect the moulded plug and 10A IEC free socket. The socket is approved to **NEMKO, NF-USE, DEMKO, CEBEC, BSI, IMQ, VDE, SEV, KEMA-KEUR, FI, OVE**, and **SEMKO** Current rating.

### Cable and Connector housings

- LEAD, AUSTRALIAN BLACK 2.5M (8.2FT)
- Connector type A: 10A Australian Plug
- Connector type B: IEC C13 Socket
- Length, lead: 2.5m
- Cable type: SVT3X18
- Voltage rating, AC: 250V
- Colour: Black
- Approval Bodies: BSI, VDE, NF-USE, OVE, CEBEG, NEMKO, DEMKO, SEMKO, IMQ, SEV, KEMA-KEUR

- Approval category: AUS AS3112-1990/NZ NZSS198-1967
- Area, conductor CSA: 1mm<sup>2</sup>
- Current rating: 10A
- Diameter, cable max: 7.2mm
- Diameter, cable min: 6.9mm
- Material: PVC
- Material, plug body: PVC