


**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [2092090003](#)  
**Status:** **Active**  
**Overview:** [L1NK Connector System](#)  
**Description:** L1NK 300 Receptacle Housing, Single Row, 3 Circuits, UL 94V-0, Black

**Documents:**

<a href="#">3D Model</a>	<a href="#">Packaging Specification 2092090000-PK-000 (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">Test Summary 2092080000-TS-000 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Datasheet (PDF)</a>
<a href="#">Product Specification 2092080000-PS-000 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Application Specification 2092080000-AS-000 (PDF)</a>	



**General**

Product Family	Crimp Housings
Series	<a href="#">209209</a>
Application	Power, Wire-to-Board
Overview	<a href="#">L1NK Connector System</a>
Product Name	L1NK 300
UPC	193264185696

**Physical**

Circuits (maximum)	3
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	0.316/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.00mm
Pitch - Termination Interface	3.00mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C

**Material Info**

**Reference - Drawing Numbers**

Application Specification	2092080000-AS-000
Packaging Specification	2092090000-PK-000
Product Specification	2092080000-PS-000
Sales Drawing	2092090000-SD-000
Test Summary	2092080000-TS-000

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2020)4578-DC (25  
June 2020)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[209209](#) Series

**Mates With**

L1NK 300 Header [2092080003](#)

**Use With**

L1NK 300 Female Terminal [2063960001](#) ,  
L1NK 300 TPA Retainer [2093250003](#)