

## Start Waterproof Housing

### START WATERPROOF 1200 HOUSING 2X

#### 0047923



#### Product features

- Luminaire, polycarbonate housing • Twin version, 1200mm • Protection type IP65 • Luminous flux and light colour vary depending on LED tubes used • To be used with T8 LED tubes • Easy to install with stainless steel fixing brackets included for ceiling mounting • Ideal for any industrial facilities, garages, car parks, workshops.



### PRODUCT OVERVIEW

Product name	START WATERPROOF 1200 HOUSING 2X
Technology	LED
Cap/Base	G13
Housing	PC Polycarbonate
Mount	Ceiling surface mounting
Fixture rating	Enclosed
General application	Logistics & Industry
ETIM Class	EC002892
E-number FI	4309057
Warranty	3 years
LOR (%)	75
Light source included	Fixture without Lightsource
Electrical protection	Class I
Housing colour	Grey
IP rating	IP65
IK rating	IK08
Product EAN number	5410288479231

### DATA TABLE

#### General data

Product name	START WATERPROOF 1200 HOUSING 2X
Technology	LED
Cap/Base	G13
Housing	PC Polycarbonate
Mount	Ceiling surface mounting
Fixture rating	Enclosed
General application	Logistics & Industry
ETIM Class	EC002892
E-number FI	4309057
Warranty	3 years

#### Optical data

## Start Waterproof Housing START WATERPROOF 1200 HOUSING 2X 0047923

LOR (%)	75
---------	----

### Electrical data

Light source included	Fixture without Lightsource
Electrical protection	Class I
Glow Wire Test (°C)	650

### Physical data

Housing colour	Grey
IP rating	IP65
IK rating	IK08
Diffuser finish	Transparent
Diffuser material	PC Polycarbonate
Nominal Product Length (mm)	1260
Nominal Product Width (mm)	99
Nominal Product Height (mm)	78
Weight (kg)	1.11

### Packaging

Single packaging type	Carton
Product EAN number	5410288479231
Packaging single length / height (cm)	128.0
Packaging single width (cm)	9.9
Packaging single depth (cm)	5.2
DUN14 (outer)	15410288479238
Units per outer package	1
Packaging outer length / height (cm)	128.0
Packaging outer width (cm)	9.9
Packaging outer depth (cm)	5.2

## TECHNICAL DRAWINGS

