

Mobile workbench with manual height adjustment

Solid beechwood 1500 mm, 2 drawers with full extension, height-adjustable by crank handle

Execution:

- Continuous height adjustment from approx. 740-1040 mm via hand crank (removable)
- Base made of square steel tube, outer 60 x 60 x 2 mm, inner 55 x 55 x 2 mm, with level compensation on all four feet
- Runs on 2 steering rollers and 2 fixed castors
- Steering rollers with wheel block

Advantage:

- Workbench can be quickly and easily adjusted to the desired working height
- always working at the right height ensures ideal ergonomic conditions
- Running gear makes workbench suitable for mobile use
- When you buy this product, you plant a tree and also receive a tree certificate!

Delivery:

Fully assembled including hand crank



Art. no.	50212 380
Brand	HK
Manufacturer Part Number	50212380
Number of drawers	2
Worktop width	1500 mm
Worktop height	50 mm
Pullout type	Full extension
Worktop depth	700 mm
Colour of front	Gentian blue RAL 5010
Cabinet colour	Light grey RAL 7035
Functions	RFID possible
Max. height	1040
Min. height	740
Adjustable in height	Yes
Drawer surface	0.27 m ²
With single pull-out safety brake	Yes
Surface	Powder-coated
Load-carrying capacity	800 kg
Drawer front height	1 x 150 mm, 1 x 180 mm
Type	Manual height adjustment
Material of worktop	Solid beech
Material of base frame	Steel plate
Drawer width (inner dimension)	450
Drawer depth (inner dimension)	600
Levelling	Yes
Load-carrying capacity per drawer	70 kg
Central locking	No
Gross Weight	115.000 kg
Product Group	5BC

EAN

405362535899 1