

Column-mounted slewing jib crane PRAKTIKUS PW – complete set with chain hoist

The reliable, affordable assistant for any workplace



Application:

Perfect entry-level crane

Execution:

- classification according to EN 13001 HC2 S2 HD2 for light industrial use
- power supply with round trailing cable
- lockable isolating switch
- Operating voltage: 400 V/50 Hz, control voltage: 24 V
- Electric chain hoist with manual sliding chassis – two-stage lifting speed
- Swivel range 270°

Advantage:

- Lightweight construction
- Perfect entry-level crane

Delivery:

Incl. detailed documentation



Art. no.	77110 042
Brand	VETTER
Manufacturer Part Number	PW1,25-5,0+SIXX1F-HF
Model	PRAKTIKUS PW
Type	Console assembly A
Load-carrying capacity	125 kg
Overhang	5000 mm
Max. lift height	5 m
Design	With electric chain hoist
Lifting device design	With electric chain hoist SiXX-HF
Flange width	64 mm
Swivel range	183 Degree
Colour	Daffodil yellow RAL 1007
Surface	Lacquered
Operating voltage	400 V
Cable length	3.8 m
Weight	132 kg
Max. vertical force	3 kN
Max. horizontal force	15 kN
Gross Weight	161.000 kg
Product Group	7EL