





REV.	DATE	DESCRIPTION
A	06/23/98	MODIFY INTERNAL FERRULE DIMENSION
B	09/06/06	UPDATE DRAWING FORMAT



RECOMMENDED
CABLE STRIPPING DIM'S

Amphenol Connex

BNC R/A CRIMP PLUG
(FOR RG 214/U CABLE)

DESCRIPTION	MATERIAL	FINISH	QTY	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. TOLERANCES FOR MILLIMETERS ARE: 0.5 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 - .315 = ± 0.007" .315 - 1.180 = ± 0.015" 1.180 - 4.724 = ± 0.020"	DO NOT SCALE DRAWING	APPROVALS	DATE	PART DESCRIPTION	DWG. NO.	REV.	SIZE	SCALE
8								Amphenol Connex BNC R/A CRIMP PLUG (FOR RG 214/U CABLE) PART NO. 112595	112595.DWG	B	A	NA
7					DRAWN	G.R.S.	09/06/06					
6	COVER	BRASS	NICKEL	1	CHECKED							
5	FERRULE	BRASS	NICKEL	1	ISSUED							
4	CONTACT PIN	BRASS	GOLD	1	SHEET	1 OF 1						
3	INSULATOR	TEFLON	NATURAL	1								
2	BODY	BRASS	NICKEL	1								
1												