

Yealink USB Wired Headset

Yealink UH37 is a professional USB wired headset. With a 35 mm speaker and excellent stereo sound, allowing you to have an extraordinary audio experience for calls and music. The noise reduction technology of the dual microphone allows you to have clearer calls, and the noise-isolating foam oval ear cushions deliver great passive noise cancellation. The headset is ultra-lightweight and extremely comfortable, with a skin-friendly leather headband and ear cushions to wear all-day comfort. Whether you're working remotely in the office or at home, UH37 lets you focus on your work and improve your productivity. It can work seamlessly with major UC platforms and integrate natively with Yealink IP phones.



Dual Noise-Canceling
Microphones



35 mm speaker



Brilliant audio quality



Lightweight comfort



Busylight



Call and music
Mode

Dual Noise-Canceling Microphones

The dual-microphone Noise Cancellation and Acoustic Shield Technology can intelligently shield the noise and only pick up speaker voice to send. It helps to improve the clarity and quality of the call and bring the ultimate calling experience.

Phenomenal Audio for Call and Music

With a 35 mm large size speaker, UH37 supports dynamic EQ to switch call mode or music mode automatically. You can enjoy clear and natural sound quality in call mode, spacious and detailed sound quality in music mode. The new angled ear cushion design and oval memory foam isolate the ambient noise, bringing excellent passive noise reduction and creating the best listening experience.

Ultra-lightweight & ergonomic design

UH37 weighs about 15% less than the previous USB headsets generation. UH37 is well-built with a sturdy-feeling design made of high-grade plastic reinforced by a metal frame. The skin-friendly material, soft memory foam, and the ergonomic ear-fitting design, bring you a comfortable all-day experience.

Busylight

The busylight will automatically glow red when you are on the call or in the meeting to reduce external interference and improve work efficiency. You can also manually turn on the busylight to indicate your working state directly and block outside distractions.



UH37 Dual



UH37 Mono

Main Features

- Plug-and-play- USB connectivity to Yealink IP phones, including T41S/T42S/T46S/T48S/T42U/T43U/T46U/T48U/T53/T53W/T54W/T57W/T58A/VP59 (T41S/T42S/T46S/T48S should be upgraded to version 82 or later)
- HD Voice/Wideband speaker performance
- 35 mm speaker
- Noise-canceling microphones and passive noise cancellation
- ActiveProtection technology safeguards users from acoustic injury
- Music control
- Integrated LED indicator and warning tone
- 300° bendable boom arm for easy adjustment without breaking

General

- Headset cable length: 1.2 m
- Supported operating systems: Microsoft Windows®, Apple Mac OS
- Color: Black
- Weight: UH37 Mono: 96.5 g / UH37 Dual: 139.5 g
- Operating temperature: -10°C to +50°C

Microphone

- Microphone quantity: 2
- Microphone frequency response range: 100 Hz-10 kHz
- Microphone type: ECM
- Microphone bandwidth: Wideband
- Microphone sensitivity: -44.0 dB re. 1 V/Pa

Speaker

- Speaker size: 35mm
- Speaker sensitivity: 109 dB SPL @ 1 kHz, 179 mV
- Speaker frequency response range: 20 Hz-20 kHz
- Speaker impedance: 32+/-4.8Ω, @ 1.0 kHz
- Speaker input power: Normal 10 mW, Max. 30 mW
- Speaker bandwidth: Wideband

Easy Call Management

- Answer/End/Reject/Hold a call
- Volume up/down
- Microphone mute
- Redial last outgoing call


Package Features

- Package contents
 - UH37 Mono Headset / UH37 Dual Headset
 - Carrying Case
 - Quick Start Guide
- Qty/CTN: 20 PCS
- N.W/CTN: UH37 Mono: 9.2kg / UH37 Dual: 10.94 kg
- G.W/CTN: UH37 Mono: 10.1 kg / UH37 Dual: 11.9 kg
- Giftbox size: 194 mm*207 mm*53 mm
- Carton meas: 550 mm*202 mm*220 mm

Compliance



Connection



About Yealink

Yealink (Stock Code: 300628) is a global-leading provider of Unified Communication & Collaboration Solutions specialized in video conferencing, voice communications, and collaboration, dedicated to helping every person and organization embrace the power of "Easy Collaboration, High Productivity".

With best-in-class quality, innovative technology, and user-friendly experiences, Yealink is one of the best providers in more than 140 countries and regions, ranks No.1 in the global market share of IP Phone, and is the Top 5 leader in the video conferencing market (Frost & Sullivan, 2021).

Copyright

Copyright © 2022 YEALINK(XIAMEN) NETWORK TECHNOLOGY CO., LTD.

All rights reserved. No parts of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, photocopying, recording, or otherwise, for any purpose, without the express written permission of Yealink(Xiamen) Network Technology CO., LTD.

Technical Support

Visit Yealink WIKI (<http://support.yealink.com/>) for firmware downloads, product documents, FAQ, and more. For better service, we sincerely recommend you to use Yealink Ticketing system (<https://ticket.yealink.com>) to submit all your technical issues.



YEALINK(XIAMEN) NETWORK TECHNOLOGY CO., LTD.
Web: www.yealink.com
Addr: No.1 Ling-Xia North Road, High Tech Park, Huli District, Xiamen, Fujian, P.R.C
Copyright©2022 Yealink Inc. All rights reserved.