

5


4

3

2

1

D



Description: Stright BNC Crimp Plug For RG58 Style Cable

Part No: CPMC881

Application: For Cable RG58 Style

Crimp Tool: 24-9958P

Impedance: 50 Ohms

Fequency Range: 0-4 GHz

Material: Body Brass Nickel Plated  
 Contact Brass Gold Plated  
 Insulator PTFE  
 Crimp Sleeve Brass Nickel Plated  
 Coupling Nut Zinc Nickel Plated

RoHS Compliance: Yes

Technical Detail: Refer to Emerson Document P/N 27-0000

DRAWING NO.	
CPMC881-CUST	
REVISIONS	
01	OFFICAL RELEASE
	03-05-09 Z G B Y T
02	RELEASE FOR SUPPLIER ALTER
	07-27-11 Y G Y G M L <i>Lin Ma</i> <small>Rev 0811.07.28 14:30:27 -08'00'</small>


D

C

C

B

B



**DIM OUTLINE**

**CUSTOMER COPY**

A

A

受控 CONTROLLED DOCUMENT					
编号 P/N	CPMC881-CUST	版本 Rev	02	日期 Rel'd Date	Aug4,11

TOLERANCE UNLESS OTHERWISE SPECIFIED		DRAWN BY	DATE
DECIMALS		YUGE HU	07-27-11
X	$\pm$ 0.5	CHECKED BY	DATE
X.X	$\pm$ 0.3	YUGE HU	07-27-11
X.XX	$\pm$ 0.1	APPROVED BY	DATE
ANGLES	$\pm$ 0.5°	LIN MA	07-27-11
		U/M	mm



TITLE  
**STRAIGHT BNC CRIMP PLUG FOR R58 STYLE CABLE**

THIS DRAWING WAS PRODUCED BY COMPUTER, DO NOT SCALE DRAWING OR UPDATE MANUALLY.

SHEET	DRAWING NO.	SIZE
1 OF 1	CPMC881-CUST	A

5

4

3

2

1