

## Han-Mod RJ45 IDC cable jack 8P AWG 24-22



Image is for illustration purposes only. Please refer to product description.

Part number	09 14 545 1562
Specification	Han-Mod RJ45 IDC cable jack 8P AWG 24-22
HARTING eCatalogue	<a href="https://b2b.harting.com/09145451562">https://b2b.harting.com/09145451562</a>

### Identification

Category	Inserts
Element	Data connectors
Specification	Han <sup>®</sup> RJ45 cable jack

### Version

Termination method	IDC termination
Gender	Female
Number of contacts	8

### Technical characteristics

Conductor cross-section	AWG 24 ... AWG 22
Wire outer diameter	1.7 mm
Transmission characteristics	Cat. 6 <sub>A</sub> Class E <sub>A</sub> up to 500 MHz
Data rate	10 Mbit/s 100 Mbit/s 1 Gbit/s 2.5 Gbit/s 5 Gbit/s 10 Gbit/s
Limiting temperature	-40 ... +70 °C
Mating cycles	≥500
Cable diameter	5 ... 9 mm

### Material properties

Material (insert)	Polyamide (PA)
-------------------	----------------



Pushing Performance  
Since 1945

## Material properties

Material (shielding)	Zinc die-cast, nickel-plated
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

## Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
Approvals	DNV GL

## Commercial data

Packaging size	1
Net weight	20 g
Country of origin	Latvia
European customs tariff number	85389099
GTIN	5713140021587
ETIM	EC000438
eCl@ss	27440218 Module for industrial connectors (data)