



28194 5 Pc. Drive-Loc VI Interchangeable Blade Set, In Durable Pouch Set includes Drive-Loc VI handle & 4 interchangeable blades.

Item No. 28194 lbs. ↔
Slotted: 3.5+4.5, 5.5+6.5 .80
Phillips: 1+2 **Square:** 1+2
 SoftFinish® Cushion Grip Blade Lock Handle



28197 6 Pc. Drive-Loc VI Interchangeable Blade Set, In Durable Pouch Set includes Drive-Loc VI handle & 5 interchangeable blades.

Item lbs. ↔
No. 28197 .83
Security TORX®: T6s+T8s, T7s+T9s, T10s+T15s, T20s+T25s, T30s+T40s
 SoftFinish® Cushion Grip Blade Lock Handle



28199 10 Pc. Drive-Loc VI Interchangeable Blade Set, In Durable Pouch Set includes Drive-Loc VI handle & 9 interchangeable blades.

Item No. 28199 lbs. ↔
Slot/Ph: 4.0+1, 6.0+2 1.11
TORX®: T6+T8, T7+T9, T10+T15, T20+T25
Hex Inch: 3/32+7/64, 1/8+9/64, 5/32+3/16"
 SoftFinish® Cushion Grip Blade Lock Handle



28189 15 Pc. Drive-Loc VI Interchangeable Blade Set, In Durable Pouch Set includes Drive-Loc VI handle & 14 interchangeable blades.

Item No. 28189 lbs. ↔ 1.75
Slotted: 3.5+4.5, 5.5+6.5 **Phillips:** 1+2
Security TORX®: T6s+T8s, T7s+T9s, T10s+T15s, T20s+T25s, T30s+T40s
Hex Inch: 3/32+7/64, 1/8+9/64, 5/32+3/16
Hex Metric: 2.0+2.5, 3.0+4.0, 5.0+6.0mm
 SoftFinish® Cushion Grip Blade Lock Handle

Wiha MicroFinish Handle - Non-Slip Grip

Wiha MicroFinish handle has a patented non-slip surface - It won't peel, crack or deteriorate when exposed to petroleum solvents. Oil and moisture flow away from the handle surface for a powerful, non-slip grip. Get maximum force & comfort with dry, oily or wet hands.

Safe, high density material, eliminates risk of sharp objects becoming embedded in the handle

Through hardened blades & hard chrome finish

Exact fit precision ground tips

Hex bolster & steel strike cap on 533 & 534 series

CVM, hardened & tempered tool steel blade, gives exceptional tool life, wear resistance & high torque performance



520 Slotted Screwdriver, With Wiha-MicroFinish Handle

Blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-MicroFinish handle, cellulose-acetate, impact resistant, non-slip, oil and grease resistant. Round blades.

Item No.	mm	Inch	mm	Inch	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
52005*	4.0	.157	100	3.9	0.8	.031	211	8.3	30	1.18	.16	10
52010*	4.0	.157	150	5.9	0.8	.031	261	10.3	30	1.18	.17	10
52020*	5.5	.216	125	5.0	1.0	.039	236	9.3	30	1.18	.20	10
52025*	5.5	.216	150	5.9	1.0	.039	261	10.3	30	1.18	.21	10
52035	6.5	.255	150	5.9	1.2	.047	268	10.6	36	1.42	.28	10
52040	8.0	.315	150	5.9	1.2	.047	274	10.8	41	1.61	.37	10
52050	10.0	.393	200	8.0	1.6	.063	324	12.8	41	1.61	.50	10

*Cabinet Tips



521 Phillips Screwdriver, With Wiha-MicroFinish Handle

Item No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
52105	1	80	3.1	191	7.5	30	1.18	.15	10
52110	1	200	8.0	311	12.2	30	1.18	.21	10
52115	2	100	3.9	218	8.6	36	1.42	.26	10
52120	2	200	8.0	318	12.5	36	1.42	.34	10
52125	3	150	5.9	274	10.8	41	1.61	.41	10



52090 5 Piece Slotted & Phillips

Screwdriver Set Blade CVM steel, hardened, hard chromed.

Item No.	Slotted:	lbs.
52090	4.0x100, 5.5x125, 8.0x150mm	1.23



52097 7 Pc. Slotted/Phillips Screwdriver Set

Item No.	Slotted:	lbs.
52097	4.0x100, 5.5x125, 8.0x150mm	1.35
	Phillips: #1x80, #1x200, #2x100, #2x200mm	

52099 12 Piece MicroFinish® Slotted & Phillips Screwdriver Set

Item No.	Slotted:	lbs.
52099	4.0x100, 5.5x125, 8.0x150, 10.0x200mm	4.20
	Phillips: 1x80, 1x200, 2x100, 2x200, 3x150mm	



52098 8 Pc. Slotted/Phillips Screwdriver Set

Item No.	Slotted:	lbs.
52098	4.0x100, 5.5x125, 6.5, 8.0x150, 10.0x200mm	2.58
	Phillips: 1x80, 2x100, 3x150mm	