



Tapered nose for easy working in confined areas and close tip cutting. Short jaws and beveled cutting edges permit close cutting of wire. Induction-hardened cutting knives for long life. Hot-riveted joint ensures smooth action and not handle wobble. Plastic-dipped handles for comfort and ease of identification. Custom, US-made tool steel.

Specifications

Type:	Standard Diagonal-Cutting Pliers	Overall Length:	5.063" (128.6 mm)
Material:	Steel	Nose Type:	Tapered
Jaw Length:	0.688" (17.5 mm)	Jaw Width:	0.563" (14.3 mm)
Jaw Thickness:	11/16" (17.5 mm)	Jaw Capacity:	1-3/64" (26.6 mm)
Cutting Knives:	Standard	Cut Style:	Standard
Joint Type:	Hot-Riveted	Handle Colour:	Red
Handle Finish:	Plastic-dipped	Handle Length:	3.75" (95.3 mm)
Insulated:	No	Tether capable:	No
Weight:	0.20 lb (0.09 kg)		