

**Specifications:**

Impedance ( $\Omega$ )	$8 \pm 15\%$ at 1000 Hz at 1.0 V
Rated Power (W)	0.2
Max Power (W)	0.3
Resonance Freq Fo (Hz)	$520 \pm 20\%$ at 1.0 V
Frequency Range (Hz)	Fo ~ 6500
Output S.P.L. (dB)	$92 \pm 3$ at .2w/.1m 1.0k, 1.2k, 1.5k, 2.0kHZ $79 \pm 3$ at 1w/1m 1.0k, 1.2k, 1.5k, 2.0kHZ
Frame Material	Metal
Operating Temp	-20 to 55°C
Weight (g)	5.0
Options	For other options contact factory

**Dimensions:  $\pm 0.3$**  (units: mm)

**ROHS Compliant**

